

# Technical Details



1.4 to 2.4 Inches 09-0102 & 09-0429			
Measuring Range		Anvil	Washer
1.40	1.42	1.4	
1.42	1.44	1.4	0.02
1.44	1.46	1.4	0.04
1.46	1.48	1.4	0.02 + 0.04
1.48	1.50	1.4	0.08
1.50	1.52	1.4	0.08 + 0.02
1.52	1.54	1.4	0.12
1.54	1.56	1.4	0.12 + 0.02
1.56	1.58	1.4	0.12 + 0.04
1.58	1.60	1.4	0.12 + 0.04 + 0.02
1.60	1.62	1.6	
1.62	1.64	1.6	0.02
1.64	1.66	1.6	0.04
1.66	1.68	1.6	0.02 + 0.04
1.68	1.70	1.6	0.08
1.70	1.72	1.6	0.08 + 0.02
1.72	1.74	1.6	0.12
1.74	1.76	1.6	0.12 + 0.02
1.76	1.78	1.6	0.12 + 0.04
1.78	1.80	1.6	0.12 + 0.04 + 0.02
1.80	1.82	1.8	
1.82	1.84	1.8	0.02
1.84	1.86	1.8	0.04
1.86	1.88	1.8	0.02 + 0.04
1.88	1.90	1.8	0.08
1.90	1.92	1.8	0.08 + 0.02
1.92	1.94	1.8	0.12
1.94	1.96	1.8	0.12 + 0.02
1.96	1.98	1.8	0.12 + 0.04
1.98	2.00	1.8	0.12 + 0.04 + 0.02

1.4 to 2.4 Inches 09-0102 & 09-0429			
Measuring Range		Anvil	Washer
2.00	2.02	2.0	
2.02	2.04	2.0	0.02
2.04	2.06	2.0	0.04
2.06	2.08	2.0	0.02 + 0.04
2.08	2.10	2.0	0.08
2.10	2.12	2.0	0.08 + 0.02
2.12	2.14	2.0	0.12
2.14	2.16	2.0	0.12 + 0.02
2.16	2.18	2.0	0.12 + 0.04
2.18	2.20	2.0	0.12 + 0.04 + 0.02
2.20	2.22	2.2	
2.22	2.24	2.2	0.02
2.24	2.26	2.2	0.04
2.26	2.28	2.2	0.02 + 0.04
2.28	2.30	2.2	0.08
2.30	2.32	2.2	0.08 + 0.02
2.32	2.34	2.2	0.12
2.34	2.36	2.2	0.12 + 0.02
2.36	2.38	2.2	0.12 + 0.04
2.38	2.40	2.2	0.12 + 0.04 + 0.02
2.40	2.42	2.4	
2.42	2.44	2.4	0.02
2.44	2.46	2.4	0.04
2.46	2.48	2.4	0.02 + 0.04
2.48	2.50	2.4	0.08
2.50	2.52	2.4	0.08 + 0.02
2.52	2.54	2.4	0.12
2.54	2.56	2.4	0.12 + 0.02
2.56	2.58	2.4	0.12 + 0.04
2.58	2.60	2.4	0.12 + 0.04 + 0.02

