

# Technical Details



18 to 35 millimeters 09-0402 & 09-0411			
Measuring Range		Anvil	Washer
18.0	18.5	18	
18.5	19.0	18	0.5
19.0	19.5	18	1.0
19.5	20.0	18	0.5 + 1.0
20.0	20.5	20	
20.5	21.0	20	0.5
21.0	21.5	20	1.0
21.5	22.0	20	0.5 + 1.0
22.0	22.5	22	
22.5	23.0	22	0.5
23.0	23.5	22	1.0
23.5	24.0	22	0.5 + 1.0
24.0	24.5	24	
24.5	25.0	24	0.5
25.0	25.5	24	1.0
25.5	26.0	24	0.5 + 1.0
26.0	26.5	26	
26.5	27.0	26	0.5

18 to 35 millimeters 09-0402 & 09-0411			
Measuring Range		Anvil	Washer
27.0	27.5	26	1.0
27.5	28.0	26	.5 + 1.0
28.0	28.5	28	
28.5	29.0	28	0.5
29.0	29.5	28	1.0
29.5	30.0	28	0.5 + 1.0
30.0	30.5	30	
30.5	31.0	30	0.5
31.0	31.5	30	1.0
31.5	32.0	30	0.5 + 1.0
32.0	32.5	32	
32.5	33.0	32	0.5
33.0	33.5	32	1.0
33.5	34.0	32	0.5 + 1.0
34.0	34.5	34	
34.5	35.0	34	0.5
35.0	35.5	34	1.0
35.5	36.0	34	0.5 + 1.0

