


Technical Details



HIGH SPEED ECONOMICAL LIVE CENTER :

FEATURES

- Accuracy guaranteed to 0.002mm TIR (0.0001")
- Excellent for CNC, grinder and high speed light-duty machining.
- Shaft extension type; improve tool clearance and machining flexibility.
- High RPM (Up to 6,000)
- Heat-treated point to HRc 60 ± 2.
- Based on double angular contact bearings for superior performance.
- Anti-friction seal for coolant deflectors and high speed.
- Heat-treated body for extra strength, rigidity and long life.



Extended Type



Dimension

Unit: mm, kg

MODEL	MT	A	B	C	LH	E	F	G	PL	L	Workpiece Weight	Max, R.P.M	Weight	Max, Run Out
05-0262	3	50	20	85	58	37	4.5	10	15	180	500	6,000	1.9	0.002
05-0263	4	66	31	107	71	63.5	5.3	12.5	23	241.5	900	6,000	2.4	0.002
05-0264	5	80	35	136	78	70	6.3	12.5	23.5	284	1,700	5,000	5.3	0.002

MT type

Technical data

- 3MT
- 4MT
- 5MT

