

Technical Details



35 to 60 millimeters 09-0405			
Measuring Range		Anvil	Washer
35.0	35.5	35	
35.5	36.0	35	0.5
36.0	36.5	35	1.0
36.5	37.0	35	0.5 + 1.0
37.0	37.5	35	2.0
37.5	38.0	35	2.0 + 0.5
38.0	38.5	35	3.0
38.5	39.0	35	3.0 + 0.5
39.0	39.5	35	3.0 + 1.0
39.5	40.0	35	3.0 + 1.0 + 0.5
40.0	40.5	40	
40.5	41.0	40	0.5
41.0	41.5	40	1.0
41.5	42.0	40	0.5 + 1.0
42.0	42.5	40	2.0
42.5	43.0	40	2.0 + 0.5
43.0	43.5	40	3.0
43.5	44.0	40	3.0 + 0.5
44.0	44.5	40	3.0 + 1.0
44.5	45.0	40	3.0 + 1.0 + 0.5
45.0	45.5	45	
45.5	46.0	45	0.5
46.0	46.5	45	1.0
46.5	47.0	45	0.5 + 1.0
47.0	47.5	45	2.0
47.5	48.0	45	2.0 + 0.5
48.0	48.5	45	3.0
48.5	49.0	45	3.0 + 0.5
49.0	49.5	45	3.0 + 1.0
49.5	50.0	45	3.0 + 1.0 + 0.5

35 to 60 millimeters 09-0405			
Measuring Range		Anvil	Washer
50.0	50.5	50	
50.5	51.0	50	0.5
51.0	51.5	50	1.0
51.5	52.0	50	0.5 + 1.0
52.0	52.5	50	2.0
52.5	53.0	50	2.0 + 0.5
53.0	53.5	50	3.0
53.5	54.0	50	3.0 + 0.5
54.0	54.5	50	3.0 + 1.0
54.5	55.0	50	3.0 + 1.0 + 0.5
55.0	55.5	55	
55.5	56.0	55	0.5
56.0	56.5	55	1.0
56.5	57.0	55	0.5 + 1.0
57.0	57.5	55	2.0
57.5	58.0	55	2.0 + 0.5
58.0	58.5	55	3.0
58.5	59.0	55	3.0 + 0.5
59.0	59.5	55	3.0 + 1.0
59.5	60.0	55	3.0 + 1.0 + 0.5
60.0	60.5	60	
60.5	61.0	60	0.5
61.0	61.5	60	1.0
61.5	62.0	60	0.5 + 1.0
62.0	62.5	60	2.0
62.5	63.0	60	2.0 + 0.5
63.0	63.5	60	3.0
63.5	64.0	60	3.0 + 0.5
64.0	64.5	60	3.0 + 1.0
64.5	65.0	60	3.0 + 1.0 + 0.5

