

Technical Details




HIGH SPEED ECONOMICAL LIVE CENTER :

Standard Type

FEATURES

- Accuracy guaranteed to 0.002mm TIR (0.0001")
- Excellent for CNC, grinder and high speed machining
- High RPM (Up to 6,000)
- Heat-treated point to HRc 60 ± 2.
- Based on double angular contact bearings for superior performance.
- Anti-friction seal for coolant deflectors and high speed.
- Heat-treated body for extra strength, rigidity and long life.



Dimension

Unit: mm. kg

MODEL	MT	A	B	C	D	E	F	L	Workpiece Weight	Max, R.P.M	Weight	Max, Run Out
04-0177	3	50	20	85	58	23	4.5	166	750	6,000	1.9	0.002
04-0178	4	66	30	108	71	35.0	5.3	211.5	1,300	6,000	2.4	0.002
04-0179	5	80	35	136	76	38	6.3	252	2,000	5,000	5.3	0.002

MT type

Technical data

- 3MT
- 4MT
- 5MT

