


These instructions provide important information on how to set up and use the electronic edge finder. Failure to follow these instructions may result in improper use of the product, which can cause damage to the product, harm to yourself or others, and may void the warranty.

BATTERY



Remove battery cover and insert batteries. Note the battery orientation shown in the illustration.



Batteries: UM5 1.5V(quantity 2)

CONFIRMATION OF LIGHTING


Touch a piece of bare metal between (A) and (B). The red light should turn on, confirming the continuity between A and B.




MEASURING METHOD

As soon as the ball touches the workpiece, the red lamp turns on.


Ball diameter: 10mm



Slowly bring the ball into contact with the side of the workpiece.



Avoid moving the edge finder too quickly to avoid damage.



Do not allow the workpiece to make contact with the shaft.