

Technical Details



0.7" to 1.5" Inches 09-0106 & 09-0426			
Measuring Range		Anvil	Washer
0.70	0.72	0.70	
0.72	0.74	0.70	0.02
0.74	0.76	0.70	0.04
0.76	0.78	0.70	0.02 + 0.04
0.78	0.80	0.78	
0.80	0.82	0.78	0.02
0.82	0.84	0.78	0.04
0.84	0.86	0.78	0.02 + 0.04
0.86	0.88	0.86	
0.88	0.90	0.86	0.02
0.90	0.92	0.86	0.04
0.92	0.94	0.86	0.02 + 0.04
0.94	0.96	0.94	
0.96	0.98	0.94	0.02
0.98	1.00	0.94	0.04
1.00	1.02	0.94	0.02 + 0.04
1.02	1.04	1.02	
1.04	1.06	1.02	0.02
1.06	1.08	1.02	0.04
1.08	1.10	1.02	0.02 + 0.04
1.10	1.12	1.10	
1.12	1.14	1.10	0.02

0.7" to 1.5" Inches 09-0106 & 09-0426			
Measuring Range		Anvil	Washer
1.14	1.16	1.10	0.04
1.16	1.18	1.10	0.02 + 0.04
1.18	1.20	1.18	
1.20	1.22	1.18	0.02
1.22	1.24	1.18	0.04
1.24	1.26	1.18	0.02 + 0.04
1.26	1.28	1.26	
1.28	1.30	1.26	0.02
1.30	1.32	1.26	0.04
1.32	1.34	1.26	0.02 + 0.04
1.34	1.36	1.34	
1.36	1.38	1.34	0.02
1.38	1.40	1.34	0.04
1.40	1.42	1.34	0.02 + 0.04
1.42	1.44	1.42	
1.44	1.46	1.42	0.02
1.46	1.48	1.42	0.04
1.48	1.50	1.42	0.02 + 0.04
1.50	1.52	1.50	
1.52	1.54	1.50	0.02
1.54	1.56	1.50	0.04
1.56	1.58	1.50	0.02 + 0.04

