

Technical Details



35 to 160 millimeters 09-0396			
Small Fulcrum Head			
Measuring Range	Anvil	Washer	
35.0	35.5	35	
35.5	36.0	35	0.5
36.0	36.5	35	1.0
36.5	37.0	35	0.5 + 1.0
37.0	37.5	35	2.0
37.5	38.0	35	2.0 + 0.5
38.0	38.5	35	3.0
38.5	39.0	35	3.0 + 0.5
39.0	39.5	35	3.0 + 1.0
39.5	40.0	35	3.0 + 1.0 + 0.5
40.0	40.5	40	
40.5	41.0	40	0.5
41.0	41.5	40	1.0
41.5	42.0	40	0.5 + 1.0
42.0	42.5	40	2.0
42.5	43.0	40	2.0 + 0.5
43.0	43.5	40	3.0
43.5	44.0	40	3.0 + 0.5
44.0	44.5	40	3.0 + 1.0
44.5	45.0	40	3.0 + 1.0 + 0.5
45.0	45.5	45	
45.5	46.0	45	0.5
46.0	46.5	45	1.0
46.5	47.0	45	0.5 + 1.0
47.0	47.5	45	2.0
47.5	48.0	45	2.0 + 0.5
48.0	48.5	45	3.0
48.5	49.0	45	3.0 + 0.5
49.0	49.5	45	3.0 + 1.0
49.5	50.0	45	3.0 + 1.0 + 0.5
50.0	50.5	50	
50.5	51.0	50	0.5
51.0	51.5	50	1.0
51.5	52.0	50	0.5 + 1.0
52.0	52.5	50	2.0
52.5	53.0	50	2.0 + 0.5

35 to 160 millimeters 09-0396			
Small Fulcrum Head			
Measuring Range	Anvil	Washer	
53.0	53.5	50	3.0
53.5	54.0	50	3.0 + 0.5
54.0	54.5	50	3.0 + 1.0
54.5	55.0	50	3.0 + 1.0 + 0.5
Large Fulcrum Head			
Measuring Range	Anvil	Washer	
50.0	50.5	50	
50.5	51.0	50	0.5
51.0	51.5	50	1.0
51.5	52.0	50	0.5 + 1.0
52.0	52.5	50	2.0
52.5	53.0	50	2.0 + 0.5
53.0	53.5	50	3.0
53.5	54.0	50	3.0 + 0.5
54.0	54.5	50	3.0 + 1.0
54.5	55.0	50	3.0 + 1.0 + 0.5
55.0	55.5	55	
55.5	56.0	55	0.5
56.0	56.5	55	1.0
56.5	57.0	55	0.5 + 1.0
57.0	57.5	55	2.0
57.5	58.0	55	2.0 + 0.5
58.0	58.5	55	3.0
58.5	59.0	55	3.0 + 0.5
59.0	59.5	55	3.0 + 1.0
59.5	60.0	55	3.0 + 1.0 + 0.5
60.0	60.5	60	
60.5	61.0	60	0.5
61.0	61.5	60	1.0
61.5	62.0	60	0.5 + 1.0
62.0	62.5	60	2.0
62.5	63.0	60	2.0 + 0.5
63.0	63.5	60	3.0
63.5	64.0	60	3.0 + 0.5
64.0	64.5	60	3.0 + 1.0
64.5	65.0	60	3.0 + 1.0 + 0.5

35 to 160 millimeters 09-0396			
Large Fulcrum Head			
Measuring Range	Anvil	Washer	
65.0	65.5	65	
65.5	66.0	65	0.5
66.0	66.5	65	1.0
66.5	67.0	65	0.5 + 1.0
67.0	67.5	65	2.0
67.5	68.0	65	2.0 + 0.5
68.0	68.5	65	3.0
68.5	69.0	65	3.0 + 0.5
69.0	69.5	65	3.0 + 1.0
69.5	70.0	65	3.0 + 1.0 + 0.5
70.0	70.5	70	
70.5	71.0	70	0.5
71.0	71.5	70	1.0
71.5	72.0	70	0.5 + 1.0
72.0	72.5	70	2.0
72.5	73.0	70	2.0 + 0.5
73.0	73.5	70	3.0
73.5	74.0	70	3.0 + 0.5
74.0	74.5	70	3.0 + 1.0
74.5	75.0	70	3.0 + 1.0 + 0.5
75.0	75.5	75	
75.5	76.0	75	0.5
76.0	76.5	75	1.0
76.5	77.0	75	0.5 + 1.0
77.0	77.5	75	2.0
77.5	78.0	75	2.0 + 0.5
78.0	78.5	75	3.0
78.5	79.0	75	3.0 + 0.5
79.0	79.5	75	3.0 + 1.0
79.5	80.0	75	3.0 + 1.0 + 0.5
80.0	80.5	80	
80.5	81.0	80	0.5
81.0	81.5	80	1.0
81.5	82.0	80	0.5 + 1.0
82.0	82.5	80	2.0
82.5	83.0	80	2.0 + 0.5

35 to 160 millimeters 09-0396			
Large Fulcrum Head			
Measuring Range	Anvil	Washer	
83.0	83.5	80	3.0
83.5	84.0	80	3.0 + 0.5
84.0	84.5	80	3.0 + 1.0
84.5	85.0	80	3.0 + 1.0 + 0.5
85.0	85.5	85	
85.5	86.0	85	0.5
86.0	86.5	85	1.0
86.5	87.0	85	0.5 + 1.0
87.0	87.5	85	2.0
87.5	88.0	85	2.0 + 0.5
88.0	88.5	85	3.0
88.5	89.0	85	3.0 + 0.5
89.0	89.5	85	3.0 + 1.0
89.5	90.0	85	3.0 + 1.0 + 0.5
90.0	90.5	90	
90.5	91.0	90	0.5
91.0	91.5	90	1.0
91.5	92.0	90	0.5 + 1.0
92.0	92.5	90	2.0
92.5	93.0	90	2.0 + 0.5
93.0	93.5	90	3.0
93.5	94.0	90	3.0 + 0.5
94.0	94.5	90	3.0 + 1.0
94.5	95.0	90	3.0 + 1.0 + 0.5
95.0	95.5	95	
95.5	96.0	95	0.5
96.0	96.5	95	1.0
96.5	97.0	95	0.5 + 1.0
97.0	97.5	95	2.0
97.5	98.0	95	2.0 + 0.5
98.0	98.5	95	3.0
98.5	99.0	95	3.0 + 0.5
99.0	99.5	95	3.0 + 1.0
99.5	100.0	95	3.0 + 1.0 + 0.5
100.0	100.5	100	
100.5	101.0	100	0.5



Technical Details



35 to 160 millimeters 09-0396			
Large Fulcrum Head			
Measuring Range	Anvil	Washer	
101.0	101.5	100	1.0
101.5	102.0	100	0.5+1.0
102.0	102.5	100	2.0
102.5	103.0	100	2.0+0.5
103.0	103.5	100	3.0
103.5	104.0	100	3.0+0.5
104.0	104.5	100	3.0+1.0
104.5	105.0	100	3.0+1.0+0.5
105.0	105.5	105	
105.5	106.0	105	0.5
106.0	106.5	105	1.0
106.5	107.0	105	0.5+1.0
107.0	107.5	105	2.0
107.5	108.0	105	2.0+0.5
108.0	108.5	105	3.0
108.5	109.0	105	3.0+0.5
109.0	109.5	105	3.0+1.0
109.5	110.0	105	3.0+1.0+0.5
Large Fulcrum Head with 55 mm Sub Rod			
Measuring Range	Anvil	Washer	
105.0	105.5	50	
105.5	106.0	50	0.5
106.0	106.5	50	1.0
106.5	107.0	50	0.5+1.0
107.0	107.5	50	2.0
107.5	108.0	50	2.0+0.5
108.0	108.5	50	3.0
108.5	109.0	50	3.0+0.5
109.0	109.5	50	3.0+1.0
109.5	110.0	50	3.0+1.0+0.5
110.0	110.5	55	
110.5	111.0	55	0.5
111.0	111.5	55	1.0
111.5	112.0	55	0.5+1.0
112.0	112.5	55	2.0
112.5	113.0	55	2.0+0.5

35 to 160 millimeters 09-0396			
Large Fulcrum Head with 55 mm Sub Rod			
Measuring Range	Anvil	Washer	
113.0	113.5	55	3.0
113.5	114.0	55	3.0+0.5
114.0	114.5	55	3.0+1.0
114.5	115.0	55	3.0+1.0+0.5
115.0	115.5	60	
115.5	116.0	60	0.5
116.0	116.5	60	1.0
116.5	117.0	60	0.5+1.0
117.0	117.5	60	2.0
117.5	118.0	60	2.0+0.5
118.0	118.5	60	3.0
118.5	119.0	60	3.0+0.5
119.0	119.5	60	3.0+1.0
119.5	120.0	60	3.0+1.0+0.5
120.0	120.5	65	
120.5	121.0	65	0.5
121.0	121.5	65	1.0
121.5	122.0	65	0.5+1.0
122.0	122.5	65	2.0
122.5	123.0	65	2.0+0.5
123.0	123.5	65	3.0
123.5	124.0	65	3.0+0.5
124.0	124.5	65	3.0+1.0
124.5	125.0	65	3.0+1.0+0.5
125.0	125.5	70	
125.5	126.0	70	0.5
126.0	126.5	70	1.0
126.5	127.0	70	0.5+1.0
127.0	127.5	70	2.0
127.5	128.0	70	2.0+0.5
128.0	128.5	70	3.0
128.5	129.0	70	3.0+0.5
129.0	129.5	70	3.0+1.0
129.5	130.0	70	3.0+1.0+0.5
130.0	130.5	75	
130.5	131.0	75	0.5

35 to 160 millimeters 09-0396			
Large Fulcrum Head with 55 mm Sub Rod			
Measuring Range	Anvil	Washer	
131.0	131.5	75	1.0
131.5	132.0	75	0.5+1.0
132.0	132.5	75	2.0
132.5	133.0	75	2.0+0.5
133.0	133.5	75	3.0
133.5	134.0	75	3.0+0.5
134.0	134.5	75	3.0+1.0
134.5	135.0	75	3.0+1.0+0.5
135.0	135.5	80	
135.5	136.0	80	0.5
136.0	136.5	80	1.0
136.5	137.0	80	0.5+1.0
137.0	137.5	80	2.0
137.5	138.0	80	2.0+0.5
138.0	138.5	80	3.0
138.5	139.0	80	3.0+0.5
139.0	139.5	80	3.0+1.0
139.5	140.0	80	3.0+1.0+0.5
140.0	140.5	85	
140.5	141.0	85	0.5
141.0	141.5	85	1.0
141.5	142.0	85	0.5+1.0
142.0	142.5	85	2.0
142.5	143.0	85	2.0+0.5
143.0	143.5	85	3.0
143.5	144.0	85	3.0+0.5
144.0	144.5	85	3.0+1.0
144.5	145.0	85	3.0+1.0+0.5
145.0	145.5	90	
145.5	146.0	90	0.5
146.0	146.5	90	1.0
146.5	147.0	90	0.5+1.0
147.0	147.5	90	2.0
147.5	148.0	90	2.0+0.5
148.0	148.5	90	3.0
148.5	149.0	90	3.0+0.5

35 to 160 millimeters 09-0396			
Large Fulcrum Head with 55 mm Sub Rod			
Measuring Range	Anvil	Washer	
149.0	149.5	90	3.0+1.0
149.5	150.0	90	3.0+1.0+0.5
150.0	150.5	95	
150.5	151.0	95	0.5
151.0	151.5	95	1.0
151.5	152.0	95	0.5+1.0
152.0	152.5	95	2.0
152.5	153.0	95	2.0+0.5
153.0	153.5	95	3.0
153.5	154.0	95	3.0+0.5
154.0	154.5	95	3.0+1.0
154.5	155.0	95	3.0+1.0+0.5
155.0	155.5	100	
155.5	156.0	100	0.5
156.0	156.5	100	1.0
156.5	157.0	100	0.5+1.0
157.0	157.5	100	2.0
157.5	158.0	100	2.0+0.5
158.0	158.5	100	3.0
158.5	159.0	100	3.0+0.5
159.0	159.5	100	3.0+1.0
159.5	160.0	100	3.0+1.0+0.5
160.0	160.5	105	
160.5	161.0	105	0.5
161.0	161.5	105	1.0
161.5	162.0	105	0.5+1.0
162.0	162.5	105	2.0
162.5	163.0	105	2.0+0.5
163.0	163.5	105	3.0
163.5	164.0	105	3.0+0.5
164.0	164.5	105	3.0+1.0
164.5	165.0	105	3.0+1.0+0.5

